

**TOSHIBA**

# Keep Storage Simple.



## Canvio Basics Portable Hard Drive

Storing your photos, videos, and data has never been easier. Toshiba's Canvio Basics portable hard drive offers up to 4TB<sup>1</sup> of storage space in a sleek compact casing for increased portability. Simply plug it in to start saving and accessing your files. That's storage made simple.



Image does not represent actual product.

**TOSHIBA**

# Canvio Basics

## Portable Hard Drive

The Canvio Basics offers one of the easiest ways to add storage to your computer with simple plug-and-play operation. Ready to use with your PC and no software installation required. Intuitively drag and drop files to and from your laptop or PC.

### Features



**Simple, Add-On Storage**



**Drag & Drop to Save Files**



**Sleek, Matte Black Design**



**Up to 4TB<sup>1</sup> of Storage**



**Easy Access to Your Content**



**USB Plug & Play**



**1 Year Limited Warranty<sup>3</sup>**



### Contents

- Toshiba Canvio Basics Portable Hard Drive
- USB-A to Micro-B Cable
- Quick Start Guide
- 1-year standard limited warranty<sup>3</sup>

### System Requirements<sup>4</sup>

- Formatted NTFS for Microsoft® Windows® 11, Windows® 10
- Requires reformatting for macOS® v15.0 / v14.7 / v13.7
- Available USB Port

### Specifications

- Capacity<sup>1</sup>: up to 4TB
- Interface: USB 3.2 Gen 1
- Interface Transfer Rate<sup>2</sup>:
  - Up to 5 Gbit/s (USB 3.0)
  - Up to 480 Mbit/s (USB 2.0)
- Size (mm):
  - 1TB/2TB: 78(W) x 109(L) x 14(H) mm
  - 4TB: 78(W) x 109(L) x 19.5(H) mm

### Colors

Black

### Weight (g)

- 1TB/2TB: 149
- 4TB: 217.5



Part Number	Capacity <sup>1</sup>	Colors	UPC
HDTB510XK3AA	1TB	Black	723844001339
HDTB520XK3AA	2TB	Black	723844001346
HDTB540XK3CA	4TB	Black	723844001353

To see our full line of consumer HDD storage products, visit:

[storage.toshiba.com/consumer-hdd](https://storage.toshiba.com/consumer-hdd)

<sup>1</sup> One Gigabyte (1GB) means 10<sup>9</sup> = 1,000,000,000 bytes and One Terabyte (1TB) means 10<sup>12</sup> = 1,000,000,000,000 bytes using powers of 10. A computer operating system, however, reports storage capacity using powers of 2 for the definition of 1GB = 2<sup>30</sup> = 1,073,741,824 bytes and 1TB = 2<sup>40</sup> = 1,099,511,627,776 bytes, and therefore shows less storage capacity. Available storage capacity (including examples of various media files) will vary based on file size, formatting, settings, software and operating system and other factors.

<sup>2</sup> Five (5) Gbit/s is the maximum interface transfer rate per the specifications of the Universal Serial Bus 3.0. Actual transfer rate will vary depending on your system configuration and other factors.

<sup>3</sup> One (1) year standard limited warranty applies. The warranty brochure is preloaded on the hard drive or can be viewed online at: <http://storage.toshiba.com/consumer-hdd/support/warranty-info>.

<sup>4</sup> Compatibility may vary depending on user's hardware configuration and operating system.

<sup>5</sup> Read and write speed may vary depending on the host device, read and write conditions, and file size.

Product prices, specifications, configurations, colors, components, features, and availability are subject to change without notice.

Microsoft and Windows are trademarks of the Microsoft group of companies.

Mac and macOS are trademarks of Apple Inc., registered in the U.S. and other countries.

Canvio and the Canvio logo are either trademarks or registered trademarks of Toshiba Electronic Devices & Storage Corporation in the United States and other countries. All other trademarks are the property of their respective owners.