


TOSHIBA

Ready to Store. Simple to Use.



Canvio Ready Portable Hard Drive

Keeping data storage simple, the Canvio Ready portable hard drive offers USB plug & play operation with up to 4TB¹ storage capacity to let you collect and store your favorite content with ease and convenience.




Image does not represent actual product.

TOSHIBA

Canvio Ready

Portable Hard Drive

The Canvio Ready features a sleek, compact design with a unique two-tone matte & gloss black finish that's stylish and easy to carry. This portable hard drive comes ready to use with your PC⁴ with no software to install. Simply drag and drop to save your files, and you're ready to go!

Features



Simple, Add-On Storage



Drag & Drop to Save Files



Sleek, Two-Tone Finish



Up to 4TB¹ of Storage



Easy Access to Your Content



Plug & Play USB 3.2 Gen 1 Compatible



1 Year Limited Warranty³



Contents

- Toshiba Canvio Ready Portable Hard Drive
- USB 3.0 Cable (works with USB 2.0)
- Quick Start Guide
- 1-year standard limited warranty³

System Requirements⁴

- Formatted NTFS for Microsoft® Windows® 11, Windows® 10
- Requires reformatting for macOS® v15.0 / v14.7 / v13.7
- Available USB 2.0 or USB 3.0 Port

Specifications

- Capacity¹: up to 4TB
- Interface: USB 3.0 (backwards compatible with USB 2.0)
- Interface Transfer Rate²:
 - Up to 5 Gbit/s (USB 3.0)
 - Up to 480 Mbit/s (USB 2.0)
- Size (mm):
 - 1TB/2TB: 78(W) x 109(L) x 14(H) mm
 - 4TB: 78(W) x 109(L) x 19.5(H) mm

Colors

Black

Weight (g)

- 1TB/2TB: 149
- 4TB: 217.5



<u>Part Number</u>	<u>Capacity¹</u>	<u>Colors</u>	<u>UPC</u>
HDTP310XK3AA	1TB	Black	723844000851
HDTP320XK3AA	2TB	Black	723844000868
HDTP340XK3CA	4TB	Black	723844000875

To see our full line of consumer HDD storage products, visit:

storage.toshiba.com/consumer-hdd

¹ One Gigabyte (1GB) means 10⁹ = 1,000,000,000 bytes and One Terabyte (1TB) means 10¹² = 1,000,000,000,000 bytes using powers of 10. A computer operating system, however, reports storage capacity using powers of 2 for the definition of 1GB = 2³⁰ = 1,073,741,824 bytes and 1TB = 2⁴⁰ = 1,099,511,627,776 bytes, and therefore shows less storage capacity. Available storage capacity (including examples of various media files) will vary based on file size, formatting, settings, software and operating system and other factors.

² Five (5) Gbit/s is the maximum interface transfer rate per the specifications of the Universal Serial Bus 3.0. Actual transfer rate will vary depending on your system configuration and other factors.

³ One (1) year standard limited warranty applies. The warranty brochure is preloaded on the hard drive or can be viewed online at: <http://storage.toshiba.com/consumer-hdd/support/warranty-info>.

⁴ Compatibility may vary depending on user's hardware configuration and operating system.

Product prices, specifications, configurations, colors, components, features, and availability are subject to change without notice.

Windows and Microsoft are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries.

Mac and macOS are trademarks of Apple Inc., registered in the U.S. and other countries.

Canvio and the Canvio logo are either trademarks or registered trademarks of Toshiba Electronic Devices & Storage Corporation in the United States and other countries. All other trademarks are the property of their respective owners.