TOSHIBA

Ready to Store. Simple to Use.



Canvio Ready

Portable Hard Drive

Whether you're saving family photos, school projects, or work files, the Toshiba Canvio Ready is designed to make extra storage effortless. With up to 4TB[1] of storage capacity and USB 3.2 Gen 1 connectivity, it’s built for simple, reliable storage wherever you go.




Image does not represent actual product.

TOSHIBA

Canvio Ready

Portable Hard Drive

The Canvio Ready features an easy-to-grip design with a smudge-resistant finish that's built for life on the go. This portable drive comes ready to use with your PC, with no software required. Simply drag and drop to save your files, and you're ready to go.

Made with care for the environment, the Canvio Ready includes at least 65% recycled materials in its top drive casing and outer packaging - offering a more sustainable way to store what matters.

Features

- **Frees up your PC storage**
- **Plug & Play Simplicity**
- **Better for the Environment***
- **Simple Drag & Drop Storage**
- **Easy-to-Grip Design**
- **Smudge-Resistant Finish**
- **Up to 4TB[1] Storage**
- **1 Year Limited Warranty[3]**



*Contains at least 65% recycled materials in the top drive casing and outer packaging.

TOSHIBA | Canvio Ready Portable Hard Drive

Contents

- Toshiba Canvio Ready Portable Hard Drive
- USB 3.2 Gen 1 Cable (USB-A to Micro-B)
- Quick Start Guide
- 1-year standard limited warranty[3]

System Requirements[4]

- Formatted NTFS for Microsoft® Windows® 11
- Requires reformatting for macOS v26.4 / v15.7.5 / v14.8.5
- Available USB port (USB 3.2 Gen 1 recommended)

Specifications

- Capacity[1]: up to 4TB
- Interface: USB 3.2 Gen 1 (backwards compatible with USB 2.0)
- Interface Transfer Rate[2]:
  - Up to 5 Gbit/s (USB 3.0)
- Cable Type: USB-A to Micro-B
- Size (mm):
  - 1TB/2TB: 78(W) x 109(L) x 14(H)
  - 4TB: 78(W) x 109(L) x 19.5(H)

Colors

Black

Weight (g)

- 1TB: 124
- 2TB: 147
- 4TB: 206



Part Number	Capacity[1]	Colors	UPC
HDTP410XK3AA	1TB	Black	723844003265
HDTP420XK3AA	2TB	Black	723844003272
HDTP440XK3CA	4TB	Black	723844003289

To see our full line of consumer HDD storage products, visit:

storage.toshiba.com/consumer-hdd

[1] One Gigabyte (1GB) means 10^9 = 1,000,000,000 bytes and One Terabyte (1TB) means 10^{12} = 1,000,000,000,000 bytes using powers of 10. A computer operating system, however, reports storage capacity using powers of 2 for the definition of 1GB= 2^{30} = 1,073,741,824 bytes and 1TB = 2^{40} = 1,099,511,627,776 bytes, and therefore shows less storage capacity. Available storage capacity (including examples of various media files) will vary based on file size, formatting, settings, software and operating system and other factors.
[2] Five (5) Gbit/s is the maximum interface transfer rate per the specifications of the Universal Serial Bus 3.2 Gen 1. Actual transfer rate will vary depending on your system configuration and other factors.
[3] One (1) year standard limited warranty applies. The warranty brochure is preloaded on the hard drive or can be viewed online at: http://storage.toshiba.com/consumer-hdd/support/warranty-info.
[4] Compatibility may vary depending on user's hardware configuration and operating system.
[5] Read and write speed may vary depending on the host device, read and write conditions, and file size.

Product prices, specifications, configurations, colors, components, features, and availability are subject to change without notice.
Microsoft and Windows are trademarks of the Microsoft group of companies.
macOS is a trademark of Apple Inc., registered in the U.S.and other countries and regions.
Canvio and the Canvio logo are either trademarks or registered trademarks of Toshiba Electronic Devices & Storage Corporation in the United States and other countries. All other trademarks are the property of their respective owners.

© 2026 Toshiba America Electronic Components, Inc.
All rights reserved.

2026.08.31-2849-R3.1