


TOSHIBA

Keep Creativity Flowing.

Built for high-end workstations and multimedia systems, the X300 Pro delivers high workload performance and massive capacity to streamline your production workflow so you can keep your creativity flowing.



X300 Pro Performance Internal Hard Drive

Enhance your productivity with the X300 Pro that delivers high performance with up to 22TB¹ storage capacity and supports a workload rate of up to 300TB/year⁵, allowing you to keep up with your content creation and storage demands.

Optimized to handle high-end graphics and videos, the X300 Pro hard drive delivers a fast 7200 RPM rotational speed and large cache size to help shorten response time. This drive offers time-tested quality that is backed by Toshiba's five year limited warranty⁷ and that gives you the peace of mind to create with confidence.

The X300 Pro Performance Hard Drive is here so you can create like a pro.



Image does not represent actual product.

TOSHIBA

X300 Pro Performance Internal Hard Drive

Application¹¹

- Professional desktop workstations
- Multi-media design workstations
- High end gaming computers
- High workload performance PC



Product image may represent a design model.



Powerful Versatility

Designed for professional content creators of all kinds. CMR technology⁹ for broad compatibility¹¹.



Advanced Precision

State-of-the-art actuator enables high-precision head positioning with accurate data tracking.



Capacity for More

Store your growing content libraries with up to 22TB¹ storage capacity.



Enhanced Performance

7200 RPM speed with up to 512MB cache size. Powered by Toshiba cache technology.



Optimized for High-Intensity Workload

Workload rate of up to 300 TB/yr⁵. MTTF up to 1.0 million hours⁶.



Data Protection

Ramp loading technology & built-in shock sensors to help protect your content.



Peace of Mind

Toshiba Five-year limited warranty⁷.



Capacity ¹	22TB	20TB	18TB
Model Number (Retail Packaging)	HDWR62CXZSTB	HDWR62AXZSTB	HDWR51JXZSTB
Model Number (Bulk)	HDWR62CUZSVB	HDWR62AUZSVB	HDWR51JUZSVB
Basic Specifications			
Interface	SATA 6.0 Gbit/s	SATA 6.0 Gbit/s	SATA 6.0 Gbit/s
Form Factor ²	3.5-inch	3.5-inch	3.5-inch
Advanced Format (AF)	Yes	Yes	Yes
RoHS Compatible ³	Yes	Yes	Yes
Sector Size	512e	512e	512e
Features			
Native Command Queuing (NCQ)	Yes	Yes	Yes
Shock Sensor	Yes	Yes	Yes
Toshiba Cache Technology	Yes	Yes	Yes
Ramp Loading Technology	Yes	Yes	Yes
Recording Technology ⁹	CMR	CMR	CMR
Performance			
Rotational Speed [RPM]	7,200	7,200	7,200
Cache Size [MB]	512	512	512
Reliability			
Maximum Workload Rate [TB/Year] ⁵	300	300	300
MTTF [Hours] ⁶	1,000,000	1,000,000	1,000,000
Unrecoverable Error Rate	1 per 10 ¹⁵	1 per 10 ¹⁵	1 per 10 ¹⁴
Load/Unload Cycles	300,000	300,000	300,000
Limited Warranty [Years] ⁷	5	5	5
Power Management			
Supply Voltage	5 VDC +10 % / -7 % 12 VDC ± 10 %	5 VDC +10 % / -7 % 12 VDC ± 10 %	5 VDC +10 % / -7 % 12 VDC ± 10 %
Power Consumption (Operating) [W] ¹²	8.02	8.02	7.48
Power Consumption (Active Idle-A) [W] ¹³	4.35	4.41	4.14
Environmental			
Temperature (Operating) [°C]	5 to 60 (surface)	5 to 60 (surface)	5 to 60 (surface)
Temperature (Non-Operating) [°C]	-40 to 70	-40 to 70	-40 to 70
Vibration (Operating) [m/s ²]	7.35 {0.75 G} (5 to 300 Hz) 2.45 {0.25 G} (300 to 500 Hz)	7.35 {0.75 G} (5 to 300 Hz) 2.45 {0.25 G} (300 to 500 Hz)	7.35 {0.75 G} (5 to 300 Hz) 2.45 {0.25 G} (300 to 500 Hz)
Vibration (Non-Operating) [m/s ²]	29.4 {3.0 G} (5 to 500 Hz)	29.4 {3.0 G} (5 to 500 Hz)	29.4 {3.0 G} (5 to 500 Hz)
Shock (Operating) [m/s ²]	490 {50 G} (2 ms duration)	490 {50 G} (2 ms duration)	686 {70G} (2 ms duration)
Shock (Non-Operating) [m/s ²]	1,960 {200 G} (2 ms duration)	1,960 {200 G} (2 ms duration)	2,450 {250 G} (2 ms duration)
Acoustics Idle Mode [dB]	20	20	20
Physical			
Height [mm Max.]	26.1	26.1	26.1
Length [mm Max.]	147.0	147.0	147.0
Width [mm Max.]	101.85	101.85	101.85
Weight [g Max.]	720	720	720
Bottom Holes Type ⁸	TYPE1	TYPE1	TYPE1

Capacity ¹	16TB	14TB	12TB
Model Number (Retail Packaging)	HDWR51GXZSTB	HDWR51EXZSTB	HDWR51CXZSTB
Model Number (Bulk)	HDWR51GUZSVB	HDWR51EUZSVB	HDWR51CUZSVB
Basic Specifications			
Interface	SATA 6.0 Gbit/s	SATA 6.0 Gbit/s	SATA 6.0 Gbit/s
Form Factor ²	3.5-inch	3.5-inch	3.5-inch
Advanced Format (AF)	Yes	Yes	Yes
RoHS Compatible ³	Yes	Yes	Yes
Sector Size	512e	512e	512e
Features			
Native Command Queuing (NCQ)	Yes	Yes	Yes
Shock Sensor	Yes	Yes	Yes
Toshiba Cache Technology	Yes	Yes	Yes
Ramp Loading Technology	Yes	Yes	Yes
Recording Technology ⁹	CMR	CMR	CMR
Performance			
Rotational Speed [RPM]	7,200	7,200	7,200
Cache Size [MB]	512	512	512
Reliability			
Maximum Workload Rate [TB/Year] ⁵	300	300	300
MTTF [Hours] ⁶	1,000,000	1,000,000	1,000,000
Unrecoverable Error Rate	1 per 10 ¹⁴	1 per 10 ¹⁴	1 per 10 ¹⁴
Load/Unload Cycles	300,000	300,000	300,000
Limited Warranty [Years] ⁷	5	5	5
Power Management			
Supply Voltage	5 VDC +10 % / -7 % 12 VDC ± 10 %	5 VDC +10 % / -7 % 12 VDC ± 10 %	5 VDC +10 % / -7 % 12 VDC ± 10 %
Power Consumption (Operating) [W] ¹²	7.48	7.38	6.85
Power Consumption (Active Idle-A) [W] ¹³	4.14	3.77	3.30
Environmental			
Temperature (Operating) [°C]	5 to 60 (surface)	5 to 60 (surface)	5 to 60 (surface)
Temperature (Non-Operating) [°C]	-40 to 70	-40 to 70	-40 to 70
Vibration (Operating) [m/s ²]	7.35 {0.75 G} (5 to 300 Hz) 2.45 {0.25 G} (300 to 500 Hz)	7.35 {0.75 G} (5 to 300 Hz) 2.45 {0.25 G} (300 to 500 Hz)	7.35 {0.75 G} (5 to 300 Hz) 2.45 {0.25 G} (300 to 500 Hz)
Vibration (Non-Operating) [m/s ²]	29.4 {3.0 G} (5 to 500 Hz)	29.4 {3.0 G} (5 to 500 Hz)	29.4 {3.0 G} (5 to 500 Hz)
Shock (Operating) [m/s ²]	686 {70G} (2 ms duration)	686 {70G} (2 ms duration)	686 {70G} (2 ms duration)
Shock (Non-Operating) [m/s ²]	2,450 {250 G} (2 ms duration)	2,450 {250 G} (2 ms duration)	2,450 {250 G} (2 ms duration)
Acoustics Idle Mode [dB]	20	20	20
Physical			
Height [mm Max.]	26.1	26.1	26.1
Length [mm Max.]	147.0	147.0	147.0
Width [mm Max.]	101.85	101.85	101.85
Weight [g Max.]	720	705	690
Bottom Holes Type ⁸	TYPE1	TYPE1	TYPE1

Capacity ¹	10TB	8TB
Model Number (Retail Packaging)	HDWR71AXZSTB	HDWR780XZSTB
Model Number (Bulk)	HDWR71AUZSVB	HDWR780UZSVB
Basic Specifications		
Interface	SATA 6.0 Gbit/s	SATA 6.0 Gbit/s
Form Factor ²	3.5-inch	3.5-inch
Advanced Format (AF)	Yes	Yes
RoHS Compatible ³	Yes	Yes
Sector Size	512e	512e
Features		
Native Command Queuing (NCQ)	Yes	Yes
Shock Sensor	Yes	Yes
Toshiba Cache Technology	Yes	Yes
Ramp Loading Technology	Yes	Yes
Recording Technology ⁹	CMR	CMR
Performance		
Rotational Speed [RPM]	7,200	7,200
Cache Size [MB]	512	512
Reliability		
Maximum Workload Rate [TB/Year] ⁵	300	300
MTTF [Hours] ⁶	1,000,000	1,000,000
Unrecoverable Error Rate	1 per 10 ¹⁵	1 per 10 ¹⁵
Load/Unload Cycles	600,000	600,000
Limited Warranty [Years] ⁷	5	5
Power Management		
Supply Voltage	5 VDC +10 % / -7 % 12 VDC ±10 %	5 VDC +10 % / -7 % 12 VDC ±10 %
Power Consumption (Operating) [W] ¹²	9.07	9.07
Power Consumption (Active Idle-A) [W] ¹³	5.74	5.74
Environmental		
Temperature (Operating) [°C]	5 to 60 (surface)	5 to 60 (surface)
Temperature (Non-Operating) [°C]	-40 to 70	-40 to 70
Vibration (Operating) [m/s ²]	7.35 {0.75 G} (5 to 300 Hz) 2.45 {0.25 G} (300 to 500 Hz)	7.35 {0.75 G} (5 to 300 Hz) 2.45 {0.25 G} (300 to 500 Hz)
Vibration (Non-Operating) [m/s ²]	29.4 {3.0 G} (5 to 500 Hz)	29.4 {3.0 G} (5 to 500 Hz)
Shock (Operating) [m/s ²]	686 {70G} (2 ms duration)	686 {70G} (2 ms duration)
Shock (Non-Operating) [m/s ²]	2,450 {250 G} (2 ms duration)	2,450 {250 G} (2 ms duration)
Acoustics Idle Mode [dB]	34	34
Physical		
Height [mm Max.]	26.1	26.1
Length [mm Max.]	147.0	147.0
Width [mm Max.]	101.85	101.85
Weight [g Max.]	755	755
Bottom Holes Type ⁸	TYPE1	TYPE1

Capacity ¹	6TB	4TB
Model Number (Retail Packaging)	HDWR760XZSTB	HDWR740XZSTB
Model Number (Bulk)	HDWR760UZSVB	HDWR740UZSVB
Basic Specifications		
Interface	SATA 6.0 Gbit/s	SATA 6.0 Gbit/s
Form Factor ²	3.5-inch	3.5-inch
Advanced Format (AF)	Yes	Yes
RoHS Compatible ³	Yes	Yes
Sector Size	512e	512e
Features		
Native Command Queuing (NCQ)	Yes	Yes
Shock Sensor	Yes	Yes
Toshiba Cache Technology	Yes	Yes
Ramp Loading Technology	Yes	Yes
Recording Technology ⁹	CMR	CMR
Performance		
Rotational Speed [RPM]	7,200	7,200
Cache Size [MB]	512	512
Reliability		
Maximum Workload Rate [TB/Year] ⁵	300	300
MTTF [Hours] ⁶	1,000,000	1,000,000
Unrecoverable Error Rate	1 per 10 ¹⁵	1 per 10 ¹⁵
Load/Unload Cycles	600,000	600,000
Limited Warranty [Years] ⁷	5	5
Power Management		
Supply Voltage	5 VDC +10 % / -7 % 12 VDC ±10 %	5 VDC +10 % / -7 % 12 VDC ±10 %
Power Consumption (Operating) [W] ¹²	8.19	7.43
Power Consumption (Active Idle-A) [W] ¹³	4.92	4.14
Environmental		
Temperature (Operating) [°C]	5 to 60 (surface)	5 to 60 (surface)
Temperature (Non-Operating) [°C]	-40 to 70	-40 to 70
Vibration (Operating) [m/s ²]	7.35 {0.75 G} (5 to 300 Hz) 2.45 {0.25 G} (300 to 500 Hz)	7.35 {0.75 G} (5 to 300 Hz) 2.45 {0.25 G} (300 to 500 Hz)
Vibration (Non-Operating) [m/s ²]	29.4 {3.0 G} (5 to 500 Hz)	29.4 {3.0 G} (5 to 500 Hz)
Shock (Operating) [m/s ²]	686 {70G} (2 ms duration)	686 {70G} (2 ms duration)
Shock (Non-Operating) [m/s ²]	2,450 {250 G} (2 ms duration)	2,450 {250 G} (2 ms duration)
Acoustics Idle Mode [dB]	34	34
Physical		
Height [mm Max.]	26.1	26.1
Length [mm Max.]	147.0	147.0
Width [mm Max.]	101.85	101.85
Weight [g Max.]	730	710
Bottom Holes Type ⁸	TYPE1	TYPE1

TOSHIBA

Toshiba Consumer Internal Hard Drives.

A drive for every storage application.



Image does not represent actual product.

To see our full line of consumer HDD storage products, visit:

storage.toshiba.com/consumer-hdd

¹ One Gigabyte (1GB) means $10^9 = 1,000,000,000$ bytes and One Terabyte (1TB) means $10^{12} = 1,000,000,000,000$ bytes using powers of 10. A computer operating system, however, reports storage capacity using powers of 2 for the definition of $1\text{GB} = 2^{30} = 1,073,741,824$ bytes and $1\text{TB} = 2^{40} = 1,099,511,627,776$ bytes, and therefore shows less storage capacity. Available storage capacity (including examples of various media files) will vary based on file size, formatting, settings, software and operating system and other factors. Actual formatted storage capacity may vary.

² 2.5-inch and 3.5-inch mean the form factor of HDDs. They do not indicate drive's physical size.

³ Toshiba Electronic Devices & Storage Corporation defines "RoHS-Compatible" products as products that either (i) contain no more than a maximum concentration value of 0.1% by weight in Homogeneous Materials for lead, mercury, hexavalent chromium, polybrominated biphenyls (PBBs) and polybrominated diphenyl ethers (PBDEs) and of 0.01% by weight in Homogeneous Materials for cadmium; or (ii) fall within any of the application exemptions set forth in the Annex to the RoHS Directive (Directive 2011/65/EC of the European Parliament and of the Council of 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment). "Homogeneous Material" means a material of uniform composition that cannot be mechanically disjointed (meaning separated, in principle, by mechanical actions such as unscrewing, cutting, crushing, grinding and/or abrasive processes) into different materials. Examples of "Homogeneous Materials" would be individual types of plastics, ceramics, glass, metals, alloys, paper, board, resins and coatings.

⁴ The maximum sustained data rate and interface speed may be restricted to the response speed of host system and by transmission characteristics. Read and write speed may vary depending on the host device, read and write conditions, and file size.

⁵ Annual Workload Rating: HDDs keep track of various drive usage such as power on hours, lifetime writes and lifetime reads from the host computer. With this data we calculate an Annualized Workload Rate, under 40 deg. C ambient environments, Annualized Workload Rate = (Lifetime Writes + Lifetime Reads) * (8760 / Lifetime Power On Hours) in case Power On time is 8760h or longer. Otherwise (i.e. Power On time is shorter than 8760h), Annualized Workload Rate = (Lifetime Writes + Lifetime Reads) Each drive is designed to perform up to the Annualized Workload Rate stated, after which the drive may be expected to decline. The Annualized Workload Rate in no way alters the warranty policy for such drive. Workload is defined as the amount of data written, read or verified by commands from host system.

⁶ MTTF (Mean Time to Failure) is not a guarantee or estimate of product life; it is a statistical value related to mean failure rates for a large number of products which may not accurately reflect actual operation. Actual operating life of the product may be different from the MTTF. MTTF (Mean Time to Failure) of the HDDs during its life time is 1.0 million hours and AFR (Annualized Failure Rate) is 0.88%, or 1.2 million hours and AFR is 0.73%, or 2.5 million hours and AFR is 0.35% (depending on HDD models). This assumes power-on hours are 24 x 7 in normal usage (8760 h/year power on hours, up to 180TB/year, or up to 300TB/year, or up to 550TB/year total data transfers (depending on HDD models), and average HDA surface temperature: 40°C or less). Use at case HDA surface temperature above 40°C may degrade product reliability and reduce warranty period.

⁷ Standard limited warranty applies. The warranty brochure can be viewed online at <http://storage.toshiba.com/consumer-hdd/warranty-info>.

⁸ Location of bottom mounting hole is different from product. For more information, please see the following page. <https://toshiba.semicon-storage.com/us/design-support/faq/storage-holes.html>

⁹ CMR is Conventional Magnetic Recording technology.

¹⁰ Product prices, specifications, configurations, colors, components, features, and availability are subject to change without notice.

¹¹ Compatibility may vary depending on user's hardware configuration and operating system.

¹² Operating watt is measured using 80% random read/write and 20% performance idle.

¹³ Idle is active idle.